

# Product Details

## Product: 100-B250NB3

Description: Contactor, IEC, 250A, 440V 50Hz / 480V 60Hz



### **SYSTEM VOLTAGE DATA**

---

Phases	3 Phase
--------	---------

### **CONTACTOR DATA**

---

Maximum Ampere Rating	250A
Pole Configuration	3 Poles
Enclosure Type	Open
Coil Voltage	480V 60Hz

### **OPTIONS DATA**

---

Substitute a N.C. for a N.O. Auxiliary Contact	No
---	----

### **OVERLOAD RELAY DATA**

---

Overload Relay Type	No Overload Protection
---------------------	------------------------

### **LOAD DATA [OPTIONAL]**

---

Load FLA (Nameplate Value)	0 A
NEC FLA	0 A
Minimum Required FLA	0 A

### **Recommended Spare Parts**

---

GG-475	1	COIL, 440-480V 50HZ MOLDED FOR CONTACTOR OR STARTER
GG-475	1	COIL, 440-480V 50HZ MOLDED FOR CONTACTOR OR STARTER
40782-800-01	1	KIT, THREE POLE CONTACT FOR CONTACTOR OR STARTER