

# Product Details

**Product: 100-B300NI3**

Description: Contactor,IEC,300A, 415V 50Hz



---

***SYSTEM VOLTAGE DATA***

Phases 3 Phase

---

***CONTACTOR DATA***

Maximum Ampere Rating 300A  
Pole Configuration 3 Poles  
Enclosure Type Open  
Coil Voltage 415V 50Hz

---

***OPTIONS DATA***

Substitute a N.C. for a N.O. No  
Auxiliary Contact

---

***OVERLOAD RELAY DATA***

Overload Relay Type No Overload Protection

---

***LOAD DATA [OPTIONAL]***

Load FLA (Nameplate Value) 0 A  
NEC FLA 0 A  
Minimum Required FLA 0 A

---

***Recommended Spare Parts***

GG-457 1 COIL,415V 50HZ MOLDED FOR CONTACTOR OR STARTER  
40782-801-01 1 KIT,THREE POLE CONTACT FOR CONTACTOR OR STARTER