

Product Details

Product: 100-B300NT3

Description: Contactor,IEC,300A, 240V 50Hz



SYSTEM VOLTAGE DATA

| | |
|--------|---------|
| Phases | 3 Phase |
|--------|---------|

CONTACTOR DATA

| | |
|-----------------------|-----------|
| Maximum Ampere Rating | 300A |
| Pole Configuration | 3 Poles |
| Enclosure Type | Open |
| Coil Voltage | 240V 50Hz |

OPTIONS DATA

| | |
|---|----|
| Substitute a N.C. for a N.O. Auxiliary Contact | No |
|---|----|

OVERLOAD RELAY DATA

| | |
|---------------------|------------------------|
| Overload Relay Type | No Overload Protection |
|---------------------|------------------------|

LOAD DATA [OPTIONAL]

| | |
|----------------------------|-----|
| Load FLA (Nameplate Value) | 0 A |
| NEC FLA | 0 A |
| Minimum Required FLA | 0 A |

Recommended Spare Parts

| | | |
|--------------|---|---|
| GG-442 | 1 | COIL,240V 50HZ MOLDED FOR CONTACTOR OR STARTER |
| 40782-801-01 | 1 | KIT,THREE POLE CONTACT FOR CONTACTOR OR STARTER |