

# Product Details

## Product: 1336F-A010-AN-EN

Description: 1336F AC Drive, 230VAC,10 HP, B frame,10 HP,Open ,EN, English

### ***MOTOR DATA***

---

Voltage	230V 60Hz
Torque	Constant Torque

### ***DRIVE DATA***

---

Max Output (Amps.)	34 A (200-230V)
Horsepower	10 HP
Enclosure Type	Open - IP00
Language	EN, English
Frame Size	B2

### ***Recommended Spare Parts***

---

1336-FAN-SP1A	1	Fan, 1336STEF, Frame B & Frame C
---------------	---	----------------------------------