

Product Details

Product: 1336F-A025-AN-EN

Description: 1336F AC Drive, 230VAC,25 HP,25 HP,Open ,EN, English

MOTOR DATA

Voltage	230V 60Hz
Torque	Constant Torque

DRIVE DATA

Max Output (Amps.)	77 A (200-230V)
Horsepower	25 HP
Enclosure Type	Open - IP00
Language	EN, English
Frame Size	C

Recommended Spare Parts

1336-FAN-SP1A	1	Fan, 1336STEF, Frame B & Frame C
---------------	---	----------------------------------