

# Product Details

## Product: 1336F-B015-AN-EN

Description: 1336F AC Drive, 460VAC ,15 HP,15 HP,Open ,EN, English

### ***MOTOR DATA***

---

Voltage	460V 60Hz
Torque	Constant Torque

### ***DRIVE DATA***

---

Max Output (Amps.)	24.2 A (380-460V) CT
Horsepower	15 HP
Enclosure Type	Open - IP00
Language	EN, English
Frame Size	B1

### ***Recommended Spare Parts***

---

1336F-MCB-SP1K	1	PCB, Main Control 1336F, Frames B-H
1336-BDB-SP3D	1	Base Driver Board, 1336
1336-QPRE-SP1C	1	PCB, Precharge, 1336STE, 460V, 7.5 - 30 HP, Series C & up 1336F, 460V, 15 - 30 HP
1336-BR-SP2A	1	Rect, Bridge, Diode 1336STE, 460V, 7.5 - 15 HP, 1336F, 460V, 15 HP
1336-QOUT-SP3A	3	TSTR, Assem., Output, 1336STEF, 460V, 15 HP
1336-CAP-SP6A	1	CAP, Assem., 1336STEF, 460V, 15 - 20 HP [kit consists of 2-caps]
1336-FAN-SP1A	1	Fan, 1336STEF, Frame B & Frame C