

Product Details

Product: 1336F-B040-AN-EN

Description: 1336F AC Drive, 460VAC ,40 HP,40 HP,Open ,EN, English

MOTOR DATA

Voltage	460V 60Hz
Torque	Constant Torque

DRIVE DATA

Max Output (Amps.)	60 A (380-460V) CT
Horsepower	40 HP
Enclosure Type	Open - IP00
Language	EN, English
Frame Size	C

Recommended Spare Parts

1336F-MCB-SP1K	1	PCB, Main Control 1336F, Frames B-H
1336-BDB-SP22D	1	Base Driver Board, 1336
1336-FAN-SP1A	1	Fan, 1336STEF, Frame B & Frame C