

# Product Details

## Product: 1336F-B100-AN-EN

Description: 1336F AC Drive, 460VAC ,100 HP,100 HP,Open ,EN, English

### ***MOTOR DATA***

---

Voltage	460V 60Hz
Torque	Constant Torque

### ***DRIVE DATA***

---

Max Output (Amps.)	138 A (380-460V) CT
Horsepower	100 HP
Enclosure Type	Open - IP00
Language	EN, English
Frame Size	D

### ***Recommended Spare Parts***

---

1336F-MCB-SP1K	1	PCB, Main Control 1336F, Frames B-H
1336-BDB-SP30D	1	Base Driver Board, 1336
1336-PB-SP23C	1	PCB, Precharge (SA), 1336STEF, 460V, 60 - 600 HP
1336-SN-SP3A	1	PCB, Converter Snubber (SA), 1336STEF, Frame D
1336-SN-SP6A	3	PCB, Inverter Snubber, 1336STEF, 460V, 60 - 100 HP
1336-SCR-SP1A	3	SCR, Assem. (SA), 1336STEF, 460V, 60 - X150 HP, 50 Amps
1336-QOUT-SP13A	3	TSTR, Assem., Output, 1336STEF, 460V, 100 HP
1336-MOV-SP1A	1	MOV, 1336STEFR, 460V, 60-125 - X150 HP
1336-CONV-SP16A	1	Bus Fuse Upgrade Kits, 1336STE, 300A, 460V, 100HP
1336-CAP-SP11A	6	CAP, Qty1, 1336STEFR, Frame D, 460 Volt
1336-FAN-SP2A	1	Fan, 1336STEFR, Frame D ( includes CHB1 Fan Capacitor )