

Product Details

Product: 1336F-B150-AN-EN

Description: 1336F AC Drive, 460VAC ,150 HP, E frame,150 HP,Open ,EN, English

MOTOR DATA

Voltage	460V 60Hz
Torque	Constant Torque

DRIVE DATA

Max Output (Amps.)	199 A (380-460V) CT
Horsepower	150 HP
Enclosure Type	Open - IP00
Language	EN, English
Frame Size	E

Recommended Spare Parts

1336F-MCB-SP1K	1	PCB, Main Control 1336F, Frames B-H
1336-BDB-SP37D	1	Base Driver Board, 1336
1336-SN-SP8A	3	PCB, Converter Snubber (SA), 1336STEF, Frame E
1336-SN-SP10A	3	PCB, Inverter Snubber, 1336STEF, 460V, 150 - 250 HP
1336-SCR-SP7A	3	SCR, Input (SA), 1336STEF, 460V, 150 - 250 HP
1336-QOUT-SP18A	3	TSTR, Assem., Output, 1336STEF, 460V, Frame E, 2 /kit includes--qty 2--Gate Interface Bds
1336-MOV-SP3A	1	MOV, 1336STEF, 460V, 150 - 250 HP
1336-F1-SP6A	1	Fuse, Bus, 1336STEF, Frame E [600A, 700V, 7.09" x 2.50"]
1336-CAP-SP12A	8	CAP, Qty1, 1336STEF, 460V, 150 - 250 HP
1336-FAN-SP3A	1	Fan, 1336STEF, Frame E (includes CHB1 Fan Capacitor)