

Product Details

Product: 1336F-BRF10-AN-EN

Description: 1336F AC Drive, 460VAC ,1 HP,1 HP,Open ,EN, English

MOTOR DATA

Voltage	460V 60Hz
Torque	Constant Torque

DRIVE DATA

Max Output (Amps.)	2.1 A (380-460V) CT
Horsepower	1 HP
Enclosure Type	Open - IP00
Language	EN, English
Frame Size	A1

Recommended Spare Parts

1336F-MCB-SP2K	1	PCB, Main Control 1336F, Frames A1-A4
1336-CAP-SP1A	1	CAP, Assem., 1336STF, 460V, 7.5 - 10 HP [kit consists of 2-caps]