

# Product Details

## Product: 1336F-BRF100-AN-EN

Description: 1336F AC Drive, 460VAC ,10 HP, A4 frame,10 HP,Open ,EN, English

### ***MOTOR DATA***

---

Voltage	460V 60Hz
Torque	Constant Torque

### ***DRIVE DATA***

---

Max Output (Amps.)	16.1 A (380-460V) CT
Horsepower	10 HP
Enclosure Type	Open - IP00
Language	EN, English
Frame Size	A4

### ***Recommended Spare Parts***

---

1336F-MCB-SP2K	1	PCB, Main Control 1336F, Frames A1-A4
1336-QOUT-SP1A	3	TSTR, Assem., Output, 1336ST, 460V, 7.5 - 10 HP