

Product Details

Product: 1336F-BRF200-AN-EN

Description: 1336F AC Drive, 460VAC, 20 HP, A4 frame, 20 HP, Open, EN, English

MOTOR DATA

Voltage	460V 60Hz
Torque	Constant Torque

DRIVE DATA

Max Output (Amps.)	27 A (380-460V) CT
Horsepower	20 HP
Enclosure Type	Open - IP00
Language	EN, English
Frame Size	A4

Recommended Spare Parts

1336F-MCB-SP2K	1	PCB, Main Control 1336F, Frames A1-A4
1336-BDB-SP4D	1	Base Driver Board, 1336
1336-QPRE-SP1C	1	PCB, Precharge, 1336STE, 460V, 7.5 - 30 HP, Series C & up 1336F, 460V, 15 - 30 HP
1336-BR-SP4A	1	Rect, Bridge, Diode, 1336STEF, 460V, 20 - 30 HP
1336-QOUT-SP5A	3	TSTR, Assem., Output, 1336STEF, 460V, 20 HP
1336-CAP-SP6A	1	CAP, Assem., 1336STEF, 460V, 15 - 20 HP [kit consists of 2-caps]