

Product Details

Product: 1336F-BRF75-AN-EN

Description: 1336F AC Drive, 460VAC ,7.5 HP, A4 frame,7.5 HP,Open ,EN, English

MOTOR DATA

Voltage	460V 60Hz
Torque	Constant Torque

DRIVE DATA

Max Output (Amps.)	13.3 A (380-460V) CT
Horsepower	7.5 HP
Enclosure Type	Open - IP00
Language	EN, English
Frame Size	A4

Recommended Spare Parts

1336F-MCB-SP2K	1	PCB, Main Control 1336F, Frames A1-A4
1336-BDB-SP1D	1	Base Driver Board, 1336
1336-BR-SP2A	1	Rect, Bridge, Diode 1336STE, 460V, 7.5 - 15 HP, 1336F, 460V, 15 HP
1336-QOUT-SP1A	3	TSTR, Assem., Output, 1336ST, 460V, 7.5 - 10 HP
1336-CAP-SP1A	1	CAP, Assem., 1336STF, 460V, 7.5 - 10 HP [kit consists of 2-caps]