

Product Details

Product: 1336F-BX060-AN-EN

Description: 1336F AC Drive, 460VAC ,60 HP,60 HP,Open ,EN, English

MOTOR DATA

Voltage	460V 60Hz
Torque	Constant Torque

DRIVE DATA

Max Output (Amps.)	77 A (380-460V) CT
Horsepower	60 HP
Enclosure Type	Open - IP00
Language	EN, English
Frame Size	C

Recommended Spare Parts

1336F-MCB-SP1K	1	PCB, Main Control 1336F, Frames B-H
1336-BDB-SP19D	1	Base Driver Board, 1336
1336-PB-SP2E	1	PCB, Precharge (SA), 1336STEF, 460V, X40 - X60 HP
1336-SN-SP1C	1	PCB, Snubber, (SA), 1336STEF, 460V, X40 - X60 SP1C (manu'f after 8-4-2000) not backwards compatible w/SP1B
1336-BR-SP10A	1	Rect, Bridge, SCR, 1336STE Series E, 1336F Series B, 460V, X40 - X60 HP
1336-QOUT-SP8A	3	TSTR, Assem., Output, 1336STEF, 460V, X40 - X60 HP
1336-F1-SP18A	1	Fuse, Bus, 1336STEF, 460V, X040 - X060 HP [200A, 700V, 5.09"x1.50"]
1336-CAP-SP9A	1	CAP, Assem., 1336STEF, 460V, X40 - X60 HP [kit cons of 6-caps]
1336-FAN-SP1A	1	Fan, 1336STEF, Frame B & Frame C