

Product Details

Product: 1336F-C125-AN-EN

Description: 1336F AC Drive, 575VAC,125 HP,125 HP,Open ,EN, English

MOTOR DATA

Voltage	575V 60Hz
Torque	Constant Torque

DRIVE DATA

Max Output (Amps.)	138 A (500-575V)
Horsepower	125 HP
Enclosure Type	Open - IP00
Language	EN, English
Frame Size	D

Recommended Spare Parts

1336-FAN-SP2A	1	Fan, 1336STEFR, Frame D (includes CHB1 Fan Capacitor)
---------------	---	---