

Product Details

Product: 1336F-CWF100-AN-EN

Description: 1336F AC Drive, 575VAC,10 HP, A4 frame,10 HP,Open ,EN, English

MOTOR DATA

Voltage	575V 60Hz
Torque	Constant Torque

DRIVE DATA

Max Output (Amps.)	12 A (500-575V)
Horsepower	10 HP
Enclosure Type	Open - IP00
Language	EN, English
Frame Size	A4