

Product: 140-CMN-9000
Description: 140-CMN MPCBs



Representative Photo Only (actual product may vary based on configuration selections)

SYSTEM VOLTAGE DATA	
Supply Voltage	480V 60Hz
CIRCUIT BREAKER	
Circuit Breaker Type	Motor Protection Circuit Breaker
Application	Normal Motor
Adj. Thermal Current Range (A)	63.0 - 90.0
UL Listed Application Ratings	UL 508 - Manual Motor Controller
FACTORY OPTIONS	
Factory Modifications, UV and Shunt Trips - Top Front Mounting	None
Factory Modifications, Auxiliary Contacts - Bottom Front Mounting	None
Factory Modifications, Trip Indicating Auxiliary Contacts - Top Front Mounting	None
SHORT CIRCUIT COORDINATION	
Short Circuit Coordination	Type 1
CERTIFICATIONS AND APPROVALS	
UL508	and CSA 22.2, No. 14 Manual Motor Controller with Optional Approvals: Group Installation, Motor Disconnect, Tap Conductor Protection Manual, Self-Protected Combination Motor Controller
EN60947-2	Circuit Breaker
EN60947-4	Overload Protection
CE	Marking is self-certified
For UL Certifications Directory:	http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm