

Product Details

Product: 1404-M605A-000

Description: Powermonitor 3000, Master Module with 3-Phase metering & setpoints & I/O, Data logging, Power quality., 5 Amps, Control Power, 120V/240V AC 50/60- Hz or 125V/250V DC, Revenue metering compliance to 0.5% Accuracy

POWERMONITOR DATA

Device Type	Master Module with 3-Phase metering & setpoints & I/O, Data logging, Power quality.
Current Inputs	5 Amps
Power Supply	Control Power, 120V/240V AC 50/60- Hz or 125V/250V DC
Communications Options	Standard RS-485 DF1 comm port