

Product Details and Certifications

Cross Reference RA Part Number: PN-D13116



Product: 140G-G-DRA

Description: Frame-G, DIN Rail Adapter, 3 Pole Adapts to 35 mm Din Rail



Representative Photo Only (actual product may vary based on configuration sections)




CIRCUIT BREAKER DATA




Bulletin Number	140G/140MG
Frame Size	G Frame
Rated Current(A)	125 A
Number of Poles	3 Poles

ACCESSORY ITEMS

Additional Accessories	(1) Frame G, DIN Adapter, Qty 1, 3 pole
------------------------	---

Accessories

	Description	Frame Size	3-Pole Cat. No.	4-Pole Cat. No.
	DIN Rail Adapter Adapts to 35 mm DIN Rail	G	140G-G-DRA	140G-G-DRA4
		H, J	140G-H-DRA	140G-H-DRA
		I	140G-I-DRA	140G-I-DRA4
	Escutcheon Plates Finish Frame with Marking provision window. For flush mounted (to door) MCCB applications.	G	140G-G-EP3	140G-G-EP4
		H	140G-H-EP3	140G-H-EP4
		I	140G-I-EP3	140G-I-EP4
		J	140G-J-EP3	140G-J-EP4
		K	140G-K-EP	
		M	140G-M-EP	
		N, NS	140G-N-EP	
R	140G-R-EP			
	IP54 Door protection Transparent plastic cover flush mounted to the enclosure door. Mounted on hinges and provided with a keyed lock.	N, NS	140G-N-BC12	
		R	140G-R-BC12	

	Description	For Use With	Cat. No.
	Adapter Plate for replacement of 140U/140M, Frames G, H, and J	140U-G to 140G-G	140G-G-PRA
		140U-H to 140G-G	
		140U-H to 140G-H	140G-J-PRA
		140U-J to 140G-J	
	Panel Mount Terminal for customer wiring connection of maintenance mode MCCBs	K, M	140G-K-CC
			140G-K-CIC
	Connector to mount shunt release in 3rd pole pocket for a 4-pole MCCB	K, M (4-pole only)	140G-K-CC2