


Product Details and Certifications

Cross Reference RA Part Number: PN-D13075

→ Product: **140G-H-PB3L**

Description: Frame-H-J, Phase Barrier, 3 pole, Qty 4, 3.94 (100mm)



Representative Photo Only (actual product may vary based on configuration selections)

CIRCUIT BREAKER DATA

Bulletin Number	Bulletin 140G/140MG
Number of Poles	3 Poles

ACCESSORY ITEMS

Phase Barriers	Frame-H-J, Phase Barrier, 3 pole, Qty 4, 3.94 (100mm)
----------------	---



CERTIFICATIONS AND APPROVALS

UL	UL489
CSA	CSA22.2 No. 5
IEC	IEC 60947-2
Certifications	UL Listed CSA Certified CE
For UL Certifications Directory:	http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm

Bulletin 140G
Molded Case Circuit Breakers
Accessories


Phase Barriers

- Provides additional clearance when special connections that extend beyond the frame of the MCCB are used.
- Frames G, H, I, J, and K are supplied with 25 mm barriers as standard.

 Representative Photo	Frame Size	Length	3-Pole Cat. No. (Pkg. Qty. 4)	4-Pole Cat. No. (Pkg. Qty. 6)
	G, I		1 in. (25 mm)	140G-G-PB3M
4 in. (100 mm)			140G-G-PB3L	140G-G-PB4L
8 in. (200 mm)			140G-G-PB3H	140G-G-PB4H
 H, J		1 in. (25 mm)	140G-H-PB3M	140G-H-PB4M
		4 in. (100 mm)	140G-H-PB3L	140G-H-PB4L
		8 in. (200 mm)	140G-H-PB3H	140G-H-PB4H
K, N, NS		4 in. (100 mm)	140G-K-PB3L	140G-K-PB4L
		8 in. (200 mm)	140G-K-PB3H	140G-K-PB4H
M		4 in. (100 mm)	140G-M-PB3L	140G-M-PB4L
R		4 in. (100 mm)	140G-R-PB3L	140G-R-PB4L
		8 in. (200 mm)	140G-R-PB3H	140G-R-PB4H

Terminal Covers

- Provide IP40 finger protection against accidental contact with live parts.
- Terminal covers are pre-punched to ease installation.
- Supplied as standard with the selection of multiple cable terminal lugs.

 Representative Photo	Frame Size	Height	3-Pole Cat. No. (Pkg. Qty. 2)	4-Pole Cat. No. (Pkg. Qty. 2)
			G	0.08 in. (2 mm)
H		2 in. (50 mm)	140G-G-TC3H	140G-G-TC4H
		0.08 in. (2 mm)	140G-H-TC3L	140G-H-TC4L
I		2 in. (50 mm)	140G-H-TC3H	140G-H-TC4H
		0.08 in. (2 mm)	140G-I-TC3L	140G-I-TC4L
J		2.36 in. (60 mm)	140G-I-TC3H	140G-I-TC4H
		0.08 in. (2 mm)	140G-J-TC3L	140G-J-TC4L
K		2.36 in. (60 mm)	140G-J-TC3H	140G-J-TC4H
		0.08 in. (2 mm)	140G-K-TC3L	140G-K-TC4L
M		2.36 in. (60 mm)	140G-K-TC3H	140G-K-TC4H
		0.08 in. (2 mm)	140G-M-TC3L	140G-M-TC4L
N, NS		2.36 in. (60 mm)	140G-M-TC3H	140G-M-TC4H
		0.1 in. (2.5 mm)	140G-N-TC3L	140G-N-TC4L
		2.76 in. (70 mm)	140G-N-TC3H	140G-N-TC4H