

Product Details and Certifications

Cross Reference RA Part Number: PN-D16501%

Product: 140G-J15C3-C&

Description: 140G - Molded Case Circuit Breaker, J frame, 100 kA, T/M - Thermal Magnetic, Rated Current 70 A



Representative Photo Only (actual product may vary based on configuration selections)

SYSTEM DATA

Supply Voltage	600V
Interrupt Rating[kA]	100 kA

CIRCUIT BREAKER DATA

Bulletin Number	140G - Molded Case Circuit Breaker
Number of Poles	3 Poles
Frame Size	J frame
Rated Current(A)	70 A
Protection	T/M - Fixed Thermal / Fixed Magnetic TMF

MANUFACTURING

Assembly	Factory Assembled
----------	-------------------

INTERNAL ACCESSORIES

Auxiliaries(AX), Alarm (AL), Auxiliary/Alarm Combination (AX/AL), Right Side Mounting	N/A
Voltage for Aux Alarm Combination	N/A



Time-Current Curves for Bulletin 140G-J
Thermo-Magnetic Molded Case Circuit Breaker

Maximum Voltage 600V AC
Maximum Current 25...50A

