

# Product Details and Certifications

Cross Reference RA Part Number: PN-D13030



Product: **140G-K-MTL63**

Description: Frame-K, Multi Terminal Lug, Qty 3, 6x6-1/0(16-50)



Representative Photo Only (actual product may vary based on configuration sections)

## ***CIRCUIT BREAKER DATA***

---

Bulletin Number	140G/140MG
Frame Size	K Frame
Number of Poles	3 Poles

## ***ACCESSORY ITEMS***

---

Terminal Lugs	Frame-K, MultiTerminal Lug, Qty 3, 6x6-1/0(16-50)
---------------	---

# Molded Case Circuit Breakers

## Accessories

### Current Transformer for Neutral Current



Representative Photo

Rated Current [A]	Frame Size	Cat. No.
300	K ★	140G-K-NCTD30
400	K ★	140G-K-NCTD40
600	M ★	140G-M-NCTD60
800	M ★	140G-M-NCTD80
400...1600	N, NS	140G-N-NCTE16
1000...3200	R	140G-R-NCTE30

★ Order with connector (Cat. No. 140G-K-CC).

### Mechanical Accessories

#### Terminal Lugs

Description	Frame Size	Cat. No. (Pkg. Qty. 3)	Cat. No. (Pkg. Qty. 4)		
<p>Representative Photo</p>	G	Cu wire, MCCB only (1) 14...1/0 AWG or 2.5...70 mm <sup>2</sup>	140G-G-TLC13	140G-G-TLC14	
		Cu wire, MCP only (1) 14...1/0 AWG or 1.5...70 mm <sup>2</sup>	140G-G-TLC13A	—	
		Multiple cable - Cu wire (6) 14...2 AWG or 2.5...35 mm <sup>2</sup>	140G-G-MTL63	140G-G-MTL64	
		Cu wire only (1) 14...1/0 AWG or 2.5...95 mm <sup>2</sup>	140G-H-TLC13	140G-H-TLC14	
<p>Representative Photo</p>	H	Multiple cable - Cu wire (6) 14...2 AWG or 2.5...35 mm <sup>2</sup>	140G-H-MTL63	140G-H-MTL64	
		Al or Cu wire (1) 14...1/0 AWG or 2.5...50 mm <sup>2</sup>	140G-I-TLA13	140G-I-TLA14	
		Al or Cu wire (1) 4...300 MCM or 25...150 mm <sup>2</sup>	140G-I-TLA1A3	140G-I-TLA1A4	
		Cu wire only (1) 10...250 MCM or 6...185 mm <sup>2</sup>	140G-I-TLC13	140G-I-TLC14	
<p>Representative Photo</p>	I	Multiple cable - Cu wire (6) 12...2 AWG or 2.5...35 mm <sup>2</sup>	140G-I-MTL63	140G-I-MTL64	
		Al or Cu wire (1) 14...1/0 AWG or 2.5...50 mm <sup>2</sup>	140G-J-TLA13	140G-J-TLA14	
		Al or Cu wire (1) 4...300 MCM or 25...150 mm <sup>2</sup>	140G-J-TLA1A3	140G-J-TLA1A4	
		Al or Cu wire (1) 6 (Al)/10 (Cu)...350 MCM or 2.5...185 mm <sup>2</sup> (Al)	140G-J-TLA1B3	140G-J-TLA1B4	
<p>Representative Photo</p>	J	Cu wire only (1) 10...350 MCM or 6...185 mm <sup>2</sup>	140G-J-TLC13	140G-J-TLC14	
		Multiple cable - Cu wire (6) 12...2 AWG or 2.5...35 mm <sup>2</sup>	140G-J-MTL63	140G-J-MTL64	
		Al or Cu wire (1) 250...500 MCM or 120...240 mm <sup>2</sup>	140G-K-TLA13	140G-K-TLA14	
		Al or Cu wire (2) 2/0...250 MCM or 95...120 mm <sup>2</sup>	140G-K-TLA23	140G-K-TLA24	
<p>Representative Photo</p>	K	Cu wire only (1) 250...500 MCM or 120...240 mm <sup>2</sup>	140G-K-TLC13	140G-K-TLC14	
		Cu wire only (2) 2/0...250 MCM or 95...120 mm <sup>2</sup>	140G-K-TLC23	140G-K-TLC24	
		Multiple cable - Cu wire (6) 6...1/0 AWG or 16...50 mm <sup>2</sup>	140G-K-MTL63	140G-K-MTL64	
		Al or Cu wire (2) 250...500 MCM or 120...240 mm <sup>2</sup>	140G-M-TLA23	140G-M-TLA24	
<p>Representative Photo</p>	M	Al or Cu wire (3) 2/0...400 MCM or 70...185 mm <sup>2</sup>	140G-M-TLA33	140G-M-TLA34	
		Cu wire only (2) 3/0...350 MCM or 85...185 mm <sup>2</sup>	140G-M-TLC23	140G-M-TLC24	
		Cu wire only (3) 2/0...350 MCM or 70...185 mm <sup>2</sup>	140G-M-TLC33	140G-M-TLC34	
		Al or Cu wire (4) 4/0...500 MCM or 70...240 mm <sup>2</sup>	140G-N-TLA43	140G-N-TLA44	
<p>Representative Photo</p>	N, NS	Cu wire only (4) 4/0...500 MCM or 70...240 mm <sup>2</sup>	140G-N-TLC43	140G-N-TLC44	
		Al or Cu wire (6) 1/0...750 MCM or 50...400 mm <sup>2</sup>	140G-R-TLA63	—	
	<p>Representative Photo</p>	R	Cu wire only (6) 1/0...750 MCM or 50...400 mm <sup>2</sup>	140G-R-TLC63	—

