

# Product Details and Certifications

Cross Reference RA Part Number: PN-D13235



Product: **140G-M-EOPJ**

Description: Frame M, Motor Operator St, 24V DC



Representative Photo Only (actual product may vary based on configuration sections)

## ***CIRCUIT BREAKER DATA***

---

Bulletin Number	140G/140MG
Rated Current (A)	800A
Frame Size	M Frame



## ***ACCESSORY ITEMS***

---

140G Frames	Fame-M, Motor Operators St, 24V DC
-------------	------------------------------------




**Direct Rotary Operators**


- Mount with direct handle operation of the MCCB.
- Lockable in OFF position (three padlocks max.).

 Representative Photo   Representative Photo	Frame Size	Handle Color	Cat. No.
	G, I	Black	140G-G-RMB
		Red/yellow	140G-G-RMY
	H, J	Black	140G-H-RMB
		Red/yellow	140G-H-RMY
	K	Black	140G-K-RMB
		Red/yellow	140G-K-RMY
	M	Black	140G-M-RMB
		Red/yellow	140G-M-RMY
	N	Black	140G-N-RMB
		Red/yellow	140G-N-RMY

**Motor Operators**

- Remotely opens, closes, and resets the MCCB.
- Frame G & I motor operators are supplied with auto/manual selector, test feature, and special tool for local operation of the MCCB.
- Frames H, J, K, and M utilize a stored energy motor for local control of the motor without the use of special tools and include auto/manual/lock selection, lever to recharge the motor, and open & close push button operation.

Description	Frame Size	Cat. No.
 Representative Photo	G, I	140G-G-EOPJ
		140G-G-EOPKY
		140G-G-EOPD
		140G-G-EOPA
		140G-G-EOPB
		140G-G-EOPC
 Representative Photo	H, J	140G-H-EOPJ
		140G-H-EOPKY
		140G-H-EOPD
		140G-H-EOPA
		140G-H-EOPB
		140G-H-EOPC
 Representative Photo	K	140G-K-EOPJ
		140G-K-EOPKY
		140G-K-EOPD
		140G-K-EOPA
		140G-K-EOPB
		140G-M-EOPJ
	M	140G-M-EOPKY
		140G-M-EOPD
		140G-M-EOPA
		140G-M-EOPB

Description	Frame Size	Cat. No.
 Representative Photo	NS	140G-NS-SCMA
		140G-NS-SCMB
		140G-NS-SCMD
		140G-NS-SCMJ
		140G-NS-SCMKY
	R	140G-R-SCMA
		140G-R-SCMD
		140G-R-SCMJ
		140G-R-SCMKY