

Product Details and Certifications

Cross Reference RA Part Number: DB!8 %) %\$)

→ Product: % \$; !B!B7 H9%

Description: Frame N-NS, Ext. Neutral Current Transformer 400..1600A



Representative Photo Only (actual product may vary based on configuration selections)

CIRCUIT BREAKER DATA

Bulletin Number	Bulletin 140G/140MG
Frame Size	N-NS frame
Rated Current(A)	400...1600 A


ACCESSORY ITEMS

Current Transformer for Neutral Current	Frame N-NS, Ext. Neutral Current Transformer 400..1600A
---	---

Molded Case Circuit Breakers

Accessories

Current Transformer for Neutral Current

 <p>Representative Photo</p>	Rated Current [A]	Frame Size	Cat. No.
	300	K ★	140G-K-NCTD30
	400	K ★	140G-K-NCTD40
	600	M ★	140G-M-NCTD60
	800	M ★	140G-M-NCTD80
	400...1600	N, NS	140G-N-NCTE16
	1000...3200	R	140G-R-NCTE30

★ Order with connector (Cat. No. 140G-K-CC).

Mechanical Accessories

Terminal Lugs

	Description	Frame Size	Cat. No. (Pkg. Qty. 3)	Cat. No. (Pkg. Qty. 4)	
 <p>Representative Photo</p>	Cu wire, MCCB only (1) 14...1/0 AWG or 2.5...70 mm ²	G	140G-G-TLC13	140G-G-TLC14	
	Cu wire, MCP only (1) 14...1/0 AWG or 1.5...70 mm ²		140G-G-TLC13A	—	
	Multiple cable - Cu wire (6) 14...2 AWG or 2.5...35 mm ²		140G-G-MTL63	140G-G-MTL64	
	 <p>Representative Photo</p>	Cu wire only (1) 14...1/0 AWG or 2.5...95 mm ²	H	140G-H-TLC13	140G-H-TLC14
Multiple cable - Cu wire (6) 14...2 AWG or 2.5...35 mm ²		140G-H-MTL63		140G-H-MTL64	
 <p>Representative Photo</p>		Al or Cu wire (1) 14...1/0 AWG or 2.5...50 mm ²	I	140G-I-TLA13	140G-I-TLA14
		Al or Cu wire (1) 4...300 MCM or 25...150 mm ²		140G-I-TLA1A3	140G-I-TLA1A4
	Cu wire only (1) 10...250 MCM or 6...185 mm ²	140G-I-TLC13		140G-I-TLC14	
	Multiple cable - Cu wire (6) 12...2 AWG or 2.5...35 mm ²	140G-I-MTL63		140G-I-MTL64	
 <p>Representative Photo</p>	Al or Cu wire (1) 14...1/0 AWG or 2.5...50 mm ²	J	140G-J-TLA13	140G-J-TLA14	
	Al or Cu wire (1) 4...300 MCM or 25...150 mm ²		140G-J-TLA1A3	140G-J-TLA1A4	
	Al or Cu wire (1) 6 (Al)/10 (Cu)...350 MCM or 2.5...185 mm ² (Al)		140G-J-TLA1B3	140G-J-TLA1B4	
	Cu wire only (1) 10...350 MCM or 6...185 mm ²		140G-J-TLC13	140G-J-TLC14	
	Multiple cable - Cu wire (6) 12...2 AWG or 2.5...35 mm ²		140G-J-MTL63	140G-J-MTL64	
 <p>Representative Photo</p>	Al or Cu wire (1) 250...500 MCM or 120...240 mm ²	K	140G-K-TLA13	140G-K-TLA14	
	Al or Cu wire (2) 2/0...250 MCM or 95...120 mm ²		140G-K-TLA23	140G-K-TLA24	
	Cu wire only (1) 250...500 MCM or 120...240 mm ²		140G-K-TLC13	140G-K-TLC14	
	Cu wire only (2) 2/0...250 MCM or 95...120 mm ²		140G-K-TLC23	140G-K-TLC24	
	Multiple cable - Cu wire (6) 6...1/0 AWG or 16...50 mm ²		140G-K-MTL63	140G-K-MTL64	
 <p>Representative Photo</p>	Al or Cu wire (2) 250...500 MCM or 120...240 mm ²	M	140G-M-TLA23	140G-M-TLA24	
	Al or Cu wire (3) 2/0...400 MCM or 70...185 mm ²		140G-M-TLA33	140G-M-TLA34	
	Cu wire only (2) 3/0...350 MCM or 85...185 mm ²		140G-M-TLC23	140G-M-TLC24	
	Cu wire only (3) 2/0...350 MCM or 70...185 mm ²		140G-M-TLC33	140G-M-TLC34	
 <p>Representative Photo</p>	Al or Cu wire (4) 4/0...500 MCM or 70...240 mm ²	N, NS	140G-N-TLA43	140G-N-TLA44	
	Cu wire only (4) 4/0...500 MCM or 70...240 mm ²		140G-N-TLC43	140G-N-TLC44	
	Al or Cu wire (6) 1/0...750 MCM or 50...400 mm ²	R	140G-R-TLA63	—	
	Cu wire only (6) 1/0...750 MCM or 50...400 mm ²	R	140G-R-TLC63	—	