

Product Details and Certifications

Cross Reference RA Part Number: PN-D13010

➔ Product: **140G-N-TLA43**

Description: Frame-N, Terminal Lug, Qty 3, FCCuAl 4x4/0-500(70-240)



Representative Photo Only (actual product may vary based on configuration selections)

CIRCUIT BREAKER DATA

Bulletin Number	Bulletin 140G/140MG
Frame Size	N frame
Rated Current(A)	1200 A
Number of Poles	3 Poles

ACCESSORY ITEMS

Terminal Lugs	Frame-N, Terminal Lug, Qty 3, FCCuAl 4x4/0-500(70-240)
---------------	--

Molded Case Circuit Breakers

Accessories

Current Transformer for Neutral Current



Representative Photo

Rated Current [A]	Frame Size	Cat. No.
300	K ★	140G-K-NCTD30
400	K ★	140G-K-NCTD40
600	M ★	140G-M-NCTD60
800	M ★	140G-M-NCTD80
400...1600	N, NS	140G-N-NCTE16
1000...3200	R	140G-R-NCTE30

★ Order with connector (Cat. No. 140G-K-CC).

Mechanical Accessories

Terminal Lugs

Description	Frame Size	Cat. No. (Pkg. Qty. 3)	Cat. No. (Pkg. Qty. 4)	
<p>Representative Photo</p>	G	Cu wire, MCCB only (1) 14...1/0 AWG or 2.5...70 mm ²	140G-G-TLC13	
		Cu wire, MCP only (1) 14...1/0 AWG or 1.5...70 mm ²	140G-G-TLC13A	
		Multiple cable - Cu wire (6) 14...2 AWG or 2.5...35 mm ²	140G-G-MTL63	
		Cu wire only (1) 14...1/0 AWG or 2.5...95 mm ²	140G-H-TLC13	
<p>Representative Photo</p>	H	Multiple cable - Cu wire (6) 14...2 AWG or 2.5...35 mm ²	140G-H-MTL63	
		Cu wire only (1) 14...1/0 AWG or 2.5...95 mm ²	140G-H-TLC14	
<p>Representative Photo</p>	I	Al or Cu wire (1) 14...1/0 AWG or 2.5...50 mm ²	140G-I-TLA13	
		Al or Cu wire (1) 4...300 MCM or 25...150 mm ²	140G-I-TLA1A3	
		Cu wire only (1) 10...250 MCM or 6...185 mm ²	140G-I-TLC13	
		Multiple cable - Cu wire (6) 12...2 AWG or 2.5...35 mm ²	140G-I-MTL63	
<p>Representative Photo</p>	J	Al or Cu wire (1) 14...1/0 AWG or 2.5...50 mm ²	140G-J-TLA13	
		Al or Cu wire (1) 4...300 MCM or 25...150 mm ²	140G-J-TLA1A3	
		Al or Cu wire (1) 6 (Al)/10 (Cu)...350 MCM or 2.5...185 mm ² (Al)	140G-J-TLA1B3	
		Cu wire only (1) 10...350 MCM or 6...185 mm ²	140G-J-TLC13	
		Multiple cable - Cu wire (6) 12...2 AWG or 2.5...35 mm ²	140G-J-MTL63	
<p>Representative Photo</p>	K	Al or Cu wire (1) 250...500 MCM or 120...240 mm ²	140G-K-TLA13	
		Al or Cu wire (2) 2/0...250 MCM or 95...120 mm ²	140G-K-TLA23	
		Cu wire only (1) 250...500 MCM or 120...240 mm ²	140G-K-TLC13	
		Cu wire only (2) 2/0...250 MCM or 95...120 mm ²	140G-K-TLC23	
		Multiple cable - Cu wire (6) 6...1/0 AWG or 16...50 mm ²	140G-K-MTL63	
<p>Representative Photo</p>	M	Al or Cu wire (2) 250...500 MCM or 120...240 mm ²	140G-M-TLA23	
		Al or Cu wire (3) 2/0...400 MCM or 70...185 mm ²	140G-M-TLA33	
		Cu wire only (2) 3/0...350 MCM or 85...185 mm ²	140G-M-TLC23	
		Cu wire only (3) 2/0...350 MCM or 70...185 mm ²	140G-M-TLC33	
<p>Representative Photo</p>	N, NS	Al or Cu wire (4) 4/0...500 MCM or 70...240 mm ²	140G-N-TLA43	
		Cu wire only (4) 4/0...500 MCM or 70...240 mm ²	140G-N-TLC43	
	<p>Representative Photo</p>	R	Al or Cu wire (6) 1/0...750 MCM or 50...400 mm ²	140G-R-TLA63
			Cu wire only (6) 1/0...750 MCM or 50...400 mm ²	140G-R-TLC63