

Product Details and Certifications

Cross Reference RA Part Number: PN-D13247

 Product: **140G-NS-SCMD**

Description: Frame NS, Charging Motor, 100-130V AC/DC



Representative Photo Only (actual product may vary based on configuration sections)




CIRCUIT BREAKER DATA


Bulletin Number	140G/140MG
Rating / Frame Size	1200A, NS-Frame

ACCESSORY ITEMS

Motor Operators	Frame NS, Charging Motor, 100-130V AC/DC
-----------------	--

Motor Operators

Description		Frame Size	Cat. No.
 <ul style="list-style-type: none"> Remotely opens, closes, and resets the MCCB. Supplied with auto/manual selector, test feature, and special tool for local operation of the MCCB. 	24V DC	G, I	140G-G-EOPJ
	48...60V DC		140G-G-EOPKY
	110...125V AC/DC		140G-G-EOPD
	220...250V AC/DC		140G-G-EOPA
	380...440V AC		140G-G-EOPB
	480...525V AC		140G-G-EOPC
 <ul style="list-style-type: none"> Remotely opens, closes, and resets the MCCB. 	24V DC	H, J	140G-H-EOPJ
	48...60V DC		140G-H-EOPKY
	110...125V AC/DC		140G-H-EOPD
	220...250V AC/DC		140G-H-EOPA
	380...440V AC		140G-H-EOPB
	480...525V AC		140G-H-EOPC
 <ul style="list-style-type: none"> Remotely opens, closes, and resets the MCCB. Uses a stored energy motor for local control of the motor without the use of special tools and include auto/manual/lock selection, lever to recharge the motor, and open & close push button operation. 	24V DC	K	140G-K-EOPJ
	48...60V DC		140G-K-EOPKY
	110...125V AC/DC		140G-K-EOPD
	220...250V AC/DC		140G-K-EOPA
	380V AC		140G-K-EOPB
	24V DC		140G-M-EOPJ
	48...60V DC	140G-M-EOPKY	M
	110...125V AC/DC	140G-M-EOPD	
	220...250V AC/DC	140G-M-EOPA	
	380V AC	140G-M-EOPB	

Description		Frame Size	Cat. No.
 <p>Spring Charging Motor</p>	24...30V AC/DC	NS	140G-NS-SCMJ
	48...60V AC/DC		140G-NS-SCMKY
	100...130V AC/DC		140G-NS-SCMD
	220...250V AC/DC		140G-NS-SCMA
	380...415V AC		140G-NS-SCMB