

Product: 140M-H8P-D10
Description: 140M MPCBs and MCPs



Representati
 Photo Only (actual product ma
 vary based on configuration
 selections)

SYSTEM VOLTAGE DATA

Supply Voltage 480V 60Hz

CIRCUIT BREAKER

Circuit Breaker Type Motor Circuit Protector
 Rated Operational Current (A) 100A
 Application Standard Magnetic Trip (Adjustable)
 Frame Size Frame Size H
 Magnetic Trip Current (A) 300 - 1100A Adjustable
 Breaking Capacity High Breaking Capacity
 UL Listed Application Ratings UL 489 Instantaneous Trip Circuit Breaker

FACTORY OPTIONS

Factory Modifications - Left Front Mounting None
 Factory Modifications - Right Front Mounting None