

Product Details and Certifications

Product: 140M-I8P-B30S

Description: MCP, Standard Magnetic Trip (Adjustable), 3 A, High Performance, Frame Size I

SYSTEM VOLTAGE DATA

Supply Voltage	600V 60Hz
Maximum Available Fault Current	5 kA

CIRCUIT BREAKER

Circuit Breaker Type	Motor Circuit Protector
Rated Operational Current (A)	3A
Application	Standard Magnetic Trip (Adjustable)
Frame Size	Frame Size I
Magnetic Trip Current (A)	9 - 30A Adjustable
Breaking Capacity	High Breaking Capacity
Overload Type	for Electronic Overloads
UL Listed Application Ratings	UL 489 Instantaneous Trip Circuit Breaker

FACTORY OPTIONS

Factory Modifications - Left Front Mounting	None
Factory Modifications - Right Front Mounting	None

TERMINAL LUG DATA

Important Information!	Stainless Steel Terminal Lugs (#14-1/0) are Factory Installed. Replacements are available for field installation. See below to order.
------------------------	------------------------------------------------------------------------------------------------------------------------------------------

Dimensions and Weight

Weight (kg / lbs)	2.00 / 4.40
-------------------	-------------