

# Product Details and Certifications

**Product:** 140M-I8P-C30

Description: MCP, Standard Magnetic Trip (Adjustable), 30 A, High Performance, Frame Size I

## **SYSTEM VOLTAGE DATA**

---

|                                 |           |
|---------------------------------|-----------|
| Supply Voltage                  | 600V 60Hz |
| Maximum Available Fault Current | 5 kA      |

## **CIRCUIT BREAKER**

---

|                               |   |
|-------------------------------|---|
| Circuit Breaker Type          | Motor Circuit Protector                   |
| Rated Operational Current (A) | 30A                                       |
| Application                   | Standard Magnetic Trip (Adjustable)       |
| Frame Size                    | Frame Size I                              |
| Magnetic Trip Current (A)     | 90 - 300A Adjustable                      |
| Breaking Capacity             | High Breaking Capacity                    |
| Overload Type                 | for Thermal Overloads                     |
| UL Listed Application Ratings | UL 489 Instantaneous Trip Circuit Breaker |

## **FACTORY OPTIONS**

---

|  |      |
|--|------|
| Factory Modifications - Left Front Mounting  | None |
| Factory Modifications - Right Front Mounting | None |

## **TERMINAL LUG DATA**

---

|                        |  |
|------------------------|--|
| Important Information! | Stainless Steel Terminal Lugs (#14-1/0) are Factory Installed.<br>Replacements are available for field installation. See below to order. |
|------------------------|--|

## **Dimensions and Weight**

---

|                   |             |
|-------------------|-------------|
| Weight (kg / lbs) | 2.00 / 4.40 |
|-------------------|-------------|