

Product Details and Certifications

Product: 140M-I8P-C30S-CX

Description: MCP, Standard Magnetic Trip (Adjustable), 30 A, High Performance, Frame Size I, (1) 1a - 1b, Lt. Side

SYSTEM VOLTAGE DATA

| | |
|---------------------------------|-----------|
| Supply Voltage | 600V 60Hz |
| Maximum Available Fault Current | 5 kA |

CIRCUIT BREAKER

| | |
|-------------------------------|---|
| Circuit Breaker Type | Motor Circuit Protector |
| Rated Operational Current (A) | 30A |
| Application | Standard Magnetic Trip (Adjustable) |
| Frame Size | Frame Size I |
| Magnetic Trip Current (A) | 90 - 300A Adjustable |
| Breaking Capacity | High Breaking Capacity |
| Overload Type | for Electronic Overloads |
| UL Listed Application Ratings | UL 489 Instantaneous Trip Circuit Breaker |

FACTORY OPTIONS

| | |
|--|--------------------------------|
| Factory Modifications - Left Front Mounting | Auxiliary Contact: (1) 1a - 1b |
| Factory Modifications - Right Front Mounting | None |

TERMINAL LUG DATA

| | |
|------------------------|--|
| Important Information! | Stainless Steel Terminal Lugs (#14-1/0) are Factory Installed. Replacements are available for field installation. See below to order. |
|------------------------|--|

Dimensions and Weight

| | |
|-------------------|-------------|
| Weight (kg / lbs) | 2.00 / 4.40 |
|-------------------|-------------|