

# Product Details and Certifications

**Product:** 140M-I8P-C50-CX

Description: MCP, Standard Magnetic Trip (Adjustable), 50 A, High Performance, Frame Size I, (1) 1a - 1b, Lt. Side

## **SYSTEM VOLTAGE DATA**

---

Supply Voltage	600V 60Hz
Maximum Available Fault Current	5 kA

## **CIRCUIT BREAKER**

---

Circuit Breaker Type	Motor Circuit Protector
Rated Operational Current (A)	50A
Application	Standard Magnetic Trip (Adjustable)
Frame Size	Frame Size I
Magnetic Trip Current (A)	150 - 500A Adjustable
Breaking Capacity	High Breaking Capacity
Overload Type	for Thermal Overloads
UL Listed Application Ratings	UL 489 Instantaneous Trip Circuit Breaker

## **FACTORY OPTIONS**

---

Factory Modifications - Left Front Mounting	Auxiliary Contact: (1) 1a - 1b
Factory Modifications - Right Front Mounting	None

## **TERMINAL LUG DATA**

---

Important Information!	Stainless Steel Terminal Lugs (#14-1/0) are Factory Installed. Replacements are available for field installation. See below to order.
------------------------	--

## **Dimensions and Weight**

---

Weight (kg / lbs)	2.00 / 4.40
-------------------	-------------