

Product Details and Certifications

Product: 140M-I8R-D15S-CX

Description: MCP, High Magnetic Trip (Adjustable), 150 A, High Performance, Frame Size I, (1) 1a - 1b, Lt. Side

SYSTEM VOLTAGE DATA

Supply Voltage	600V 60Hz
Maximum Available Fault Current	5 kA

CIRCUIT BREAKER

Circuit Breaker Type	Motor Circuit Protector
Rated Operational Current (A)	150A
Application	Standard Magnetic Trip (Adjustable)
Frame Size	Frame Size I
Magnetic Trip Current (A)	750 - 2500A Adjustable
Breaking Capacity	High Breaking Capacity
Overload Type	for Electronic Overloads
UL Listed Application Ratings	UL 489 Instantaneous Trip Circuit Breaker

FACTORY OPTIONS

Factory Modifications - Left Front Mounting	Auxiliary Contact: (1) 1a - 1b
Factory Modifications - Right Front Mounting	None

TERMINAL LUG DATA

Important Information!	Stainless Steel Terminal Lugs (#14-1/0) are Factory Installed. Replacements are available for field installation. See below to order.
------------------------	--

Dimensions and Weight

Weight (kg / lbs)	2.00 / 4.40
-------------------	-------------