

## Product Details and Certifications

**Product:** 140M-JD8P-C80-W

**Description:** MCP, Standard Magnetic Trip (Adjustable), 80 A, High Performance, Frame Size JD

### SYSTEM VOLTAGE DATA

Supply Voltage, Maximum	600V 60Hz
Maximum Available Fault Current	5kA at 600V or less

### CIRCUIT BREAKER

Circuit Breaker Type	Motor Circuit Protector
Application	Standard Magnetic Trip (Adjustable)
Rated Operational Current (A)	250A (Nominal Max FLC 80A)
Frame Size	Frame Size JD
Magnetic Trip Current (A)	500 - 1000 Adjustable
Breaking Capacity	High Breaking Capacity
Certifications	UL 489 Instantaneous Trip Circuit Breaker

### FACTORY OPTIONS

Factory Modifications - Left Front Mounting	None
Factory Modifications - Right Front Mounting	None

### TERMINAL LUG DATA

Important Information!	Terminal Lugs are Not Provided
------------------------	--------------------------------

### Dimensions and Weight

Weight (kg / lbs)	5.45 / 12.0
-------------------	-------------

---