

Product Details and Certifications

Product: 140M-JD8P-D20-W

Description: MCP, Standard Magnetic Trip (Adjustable), 200 A, High Performance, Frame Size JD

SYSTEM VOLTAGE DATA

Supply Voltage, Maximum	600V 60Hz
Maximum Available Fault Current	5kA at 600V or less

CIRCUIT BREAKER

Circuit Breaker Type	Motor Circuit Protector
Application	Standard Magnetic Trip (Adjustable)
Rated Operational Current (A)	250A (Nominal Max FLC 200A)
Frame Size	Frame Size JD
Magnetic Trip Current (A)	1250 - 2500 Adjustable
Breaking Capacity	High Breaking Capacity
Certifications	UL 489 Instantaneous Trip Circuit Breaker

FACTORY OPTIONS

Factory Modifications - Left Front Mounting	None
Factory Modifications - Right Front Mounting	None

TERMINAL LUG DATA

Important Information!	Terminal Lugs are Not Provided
------------------------	--------------------------------

Dimensions and Weight

Weight (kg / lbs)	5.45 / 12.0
-------------------	-------------
