

Product Details and Certifications

Product: 140M-K8P-D25

Description: MCP, Standard Magnetic Trip (Adjustable), 250 A, High Performance, Frame Size K

SYSTEM VOLTAGE DATA

| | |
|---------------------------------|-----------|
| Supply Voltage | 600V 60Hz |
| Maximum Available Fault Current | 5 kA |

CIRCUIT BREAKER

| | |
|-------------------------------|---|
| Circuit Breaker Type | Motor Circuit Protector |
| Rated Operational Current (A) | 250A |
| Application | Standard Magnetic Trip (Adjustable) |
| Frame Size | Frame Size K |
| Magnetic Trip Current (A) | 1250 - 2500A Adjustable |
| Breaking Capacity | High Breaking Capacity |
| UL Listed Application Ratings | UL 489 Instantaneous Trip Circuit Breaker |

FACTORY OPTIONS

| | |
|--|------|
| Factory Modifications - Left Front Mounting | None |
| Factory Modifications - Right Front Mounting | None |

TERMINAL LUG DATA

| | |
|------------------------|--|
| Important Information! | Terminal Lugs are not Factory Installed. See below to order. |
|------------------------|--|

Dimensions and Weight

| | |
|-------------------|-------------|
| Weight (kg / lbs) | 6.10 / 13.4 |
|-------------------|-------------|