

Product Details and Certifications

Product: 140M-K8P-D45

Description: MCP, Standard Magnetic Trip (Adjustable), 450 A, High Performance, Frame Size K

SYSTEM VOLTAGE DATA

Supply Voltage	600V 60Hz
Maximum Available Fault Current	5 kA

CIRCUIT BREAKER

Circuit Breaker Type	Motor Circuit Protector
Rated Operational Current (A)	450A
Application	Standard Magnetic Trip (Adjustable)
Frame Size	Frame Size K
Magnetic Trip Current (A)	2250 - 4500A Adjustable
Breaking Capacity	High Breaking Capacity
UL Listed Application Ratings	UL 489 Instantaneous Trip Circuit Breaker

FACTORY OPTIONS

Factory Modifications - Left Front Mounting	None
Factory Modifications - Right Front Mounting	None

TERMINAL LUG DATA

Important Information!	Terminal Lugs are not Factory Installed. See below to order.
------------------------	--

Dimensions and Weight

Weight (kg / lbs)	6.10 / 13.4
-------------------	-------------