

**Product:** 140M-N8P-D80

**Description:** 140M MPCBs and MCPs

**SYSTEM VOLTAGE DATA**

Supply Voltage 480V 60Hz

**CIRCUIT BREAKER**

Circuit Breaker Type	Motor Circuit Protector
Rated Operational Current (A)	800A
Application	Standard Magnetic Trip (Adjustable)
Frame Size	Frame Size N
Magnetic Trip Current (A)	1600 - 6400A Adjustable
Breaking Capacity	High Breaking Capacity
UL Listed Application Ratings	UL 489 Instantaneous Trip Circuit Breaker

**FACTORY OPTIONS**

Factory Modifications - Left Front Mounting	None
Factory Modifications - Right Front Mounting	None