

Product Details

Product: 140M-Q8P-D60

Description: MCP, Standard Magnetic Trip (Adjustable), 600 A, High Performance, Frame Size Q

SYSTEM VOLTAGE DATA

Supply Voltage	480V 60Hz
Maximum Available Fault Current	5 kA

CIRCUIT BREAKER

Circuit Breaker Type	Motor Circuit Protector
Application	Standard Magnetic Trip (Adjustable)
Rated Operational Current (A)	600A
Frame Size	Frame Size Q
Magnetic Trip Current (A)	1800 - 6000A Adjustable
Breaking Capacity	High Breaking Capacity
UL Listed Application Ratings	UL 489 Instantaneous Trip Circuit Breaker

FACTORY OPTIONS

Factory Modifications - Left Front Mounting	None
Factory Modifications - Right Front Mounting	None

TERMINAL LUG DATA

Important Information!	Terminal Lugs are not Factory Installed. See below to order.
------------------------	--

Dimensions and Weight

Weight (kg / lbs)	9.40 / 20.7
-------------------	-------------
