

Product: 140U-H2C3-C50
Description: 140U Molded Case Circuit Breakers



Representati
 Photo Only (actual product may vary based o
 configuration selections)

System Data

Supply Voltage 480V 60Hz

Circuit Breaker Data

Current Limitation Required? No
 Pole Configuration 3 Poles
 Rated Current (A) 50
 Protection T/M - Fixed Thermal / Fixed Magnetic
 Frame Size H-Frame (up to 125A)
 Interrupt Rating [kA] 25 kA

Manufacturing

Assembly Factory Assembled

Internal Control Modules, Factory Installed

Shunt Trip (SNT) and Undervoltage Release (UVT), Left Side Mounting None
 Voltage None
 Auxiliaries (AX), Alarm (AL), Auxiliary/Alarm Combination (AX/AL), Right Side Mounting None

Mounting Data

Busbar Mounting (Only for Use with 141A Mounting System) None

CERTIFICATIONS AND APPROVALS

UL 489
 CSA 22.2, No. 5
 IEC 60947-2
 CE
 KEMA-KEUR

For UL Certifications Directory: <http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm>