

**Table 1 Combination 2107, 2113, 2123, 2127, and 2173 Starter Units - I-Frame Thermal Magnetic Circuit Breakers (Non-Adjustable Magnetic Trip)**

Circuit Breaker Continuous Current Rating (Amperes)	NEMA Starter Size	Horsepower Ratings					Magnetic Trip Range (Amperes)		Medium Interrupting Capacity Suffix Letter "CB"	High Interrupting Capacity Suffix Letter "CM"	Medium Interrupting Capacity with Current Limiter Suffix Letter "CD"
		200V	230V	380 - 415V	460V	575V	Min.	Max.			
15	1	0.125 - 1.5	0.125 - 2	0.125 - 3	0.125 - 3	0.125 - 5	500	800	140U-I3C3-C15	140U-I6C3-C15	140U-I3C3-C15 140U-I-CLC70
20	1	2	3	5	5	7.5		1000	140U-I3C3-C20	140U-I6C3-C20	140U-I3C3-C20 140U-I-CLC70
30	1	3	5	7.5 - 10	7.5 - 10	10			140U-I3C3-C30	140U-I6C3-C30	140U-I3C3-C30 140U-I-CLC70
40	1 2	5 —	— —	— —	— —	15 15			140U-I3C3-C40	140U-I6C3-C40	140U-I3C3-C40 140U-I-CLC70
50	1 2	7.5 —	7.5 10	— 15	— 15 - 20	— 20 - 25	600	1200	140U-I3C3-C50	140U-I6C3-C50	140U-I3C3-C50 140U-I-CLC70
60	2 3	10 —	— —	20 —	25 —	30 —			140U-I3C3-C60	140U-I6C3-C60	140U-I3C3-C60 140U-I-CLC70
70	2 3	— —	15 —	25 —	— 30	— 40			140U-I3C3-C70	140U-I6C3-C70	140U-I3C3-C70 140U-I-CLC70
100	3	15	—	30	40	50		700	1400	140U-I3C3-D10	140U-I6C3-D10
125	3	20	20	40	50	—	800	1600	140U-I3C3-D12-S	140U-I6C3-D12-S	140U-I3C3-D12-S 140U-I-CLD15
150	3	25	25 - 30	50	—	—				140U-I3C3-D15-S	140U-I6C3-D15-S



**Table 2 Combination 2107, 2113, 2123, 2127 and 2173 Starter Units - JD-Frame and K-Frame Thermal Magnetic Circuit Breakers (Adjustable Magnetic Trip)**

Circuit Breaker Continuous Current Rating (Amperes)	NEMA Starter Size	Horsepower Ratings					Magnetic Trip Setting (Amperes)									Standard Interrupting Capacity Suffix Letter "CT"	High Interrupting Capacity Suffix Letter "CM"
		200V	230V	380 - 415V	460V	575V	5X	—	—	—	7.5X	—	—	—	10X		
125	4	—	—	—	60	60 - 75	625	700	780	860	940	1020	1050	1170	1250	140U-JD3D3-D12	140U-JD6D3-D12
150	4	30	40	60 - 75	75	100	750	840	935	1030	1125	1220	1315	1410	1500	140U-JD3D3-D15	140U-JD6D3-D15
175	4 5	40 —	50 —	— —	100 —	— 125	875	980	1090	1200	1310	1420	1530	1640	1750	140U-JD3D3-D17	140U-JD6D3-D17
250	5	50 - 60	60 - 75	100 - 125	125 - 150	150 - 200	1250	1405	1565	1720	1875	2030	2185	2340	2500	140U-JD3D3-D25	140U-JD6D3-D25
300	5	75	—	150	—	—	1500	1690	1875	2065	2250	2440	2630	2815	3000	140U-K3D3-D30	140U-K6D3-D30
400 <sup>(1)</sup>	5	—	100	—	200	—	2000	2250	2500	2750	3000	3250	3500	3750	4000	140U-K3D3-D40	140U-K6D3-D40

(1) For 460V, 125 Hp or 150 Hp specified with circuit breaker suffix "CTH" or "CMH," use the line for 400A, 460V, 200 HP.