

Product Details and Certifications

Product: 140U-I0C3-D12-S

Description: 125A Molded Case Circuit Breaker, 3-Pole, Frame Size I, High Breaking Capacity

SYSTEM VOLTAGE DATA

Supply Voltage, Maximum	600V 60Hz
Maximum Available Fault Current	200kA@240V, 100kA@480V, 35kA@600V

CIRCUIT BREAKER

Circuit Breaker Type	Molded Case Circuit Breaker
Application	Inverse Time, Thermal-Magnetic Trip (Fixed Thermal, Fixed Magnetic)
Rated Operational Current (A)	125A
Frame Size	Frame Size I
Magnetic Trip Current (A)	800A Min - 1600A Max Fixed
Breaking Capacity	High Breaking Capacity
Certifications	UL 489, CSA 22.2 No. 5

FACTORY OPTIONS

Factory Modifications - Left Front Mounting	None
Factory Modifications - Right Front Mounting	None

TERMINAL LUG DATA

Important Information!	#4AWG - #4/0 AWG, Cu
------------------------	----------------------

Dimensions and Weight

Weight (kg / lbs)	2.04 / 4.5
-------------------	------------
