

Product Details and Certifications

Product: 140U-I3C3-C40

Description: 40A Molded Case Circuit Breaker, 3-Pole, Frame Size I, Standard Breaking Capacity

SYSTEM VOLTAGE DATA

| | |
|---------------------------------|---------------------------------|
| Supply Voltage, Maximum | 600V 60Hz |
| Maximum Available Fault Current | 65kA@240V, 35kA@480V, 18kA@600V |

CIRCUIT BREAKER

| | |
|-------------------------------|---|
| Circuit Breaker Type | Molded Case Circuit Breaker |
| Application | Inverse Time, Thermal-Magnetic Trip (Fixed Thermal, Fixed Magnetic) |
| Rated Operational Current (A) | 40A |
| Frame Size | Frame Size I |
| Magnetic Trip Current (A) | 500A Min - 1000A Max Fixed |
| Breaking Capacity | Standard Breaking Capacity |
| Certifications | UL 489, CSA 22.2 No. 5 |

FACTORY OPTIONS

| | |
|--|------|
| Factory Modifications - Left Front Mounting | None |
| Factory Modifications - Right Front Mounting | None |

TERMINAL LUG DATA

| | |
|------------------------|--------------------------|
| Important Information! | #14AWG - #1/0 AWG, Cu/Al |
|------------------------|--------------------------|

Dimensions and Weight

| | |
|-------------------|------------|
| Weight (kg / lbs) | 2.04 / 4.5 |
|-------------------|------------|
