

## Product Details and Certifications

**Product:** 140U-I3C3-D12

**Description:** 125A Molded Case Circuit Breaker, 3-Pole, Frame Size I, Standard Breaking Capacity

### SYSTEM VOLTAGE DATA

Supply Voltage, Maximum	600V 60Hz
Maximum Available Fault Current	65kA@240V, 35kA@480V, 18kA@600V

### CIRCUIT BREAKER

Circuit Breaker Type	Molded Case Circuit Breaker
Application	Inverse Time, Thermal-Magnetic Trip (Fixed Thermal, Fixed Magnetic)
Rated Operational Current (A)	125A
Frame Size	Frame Size I
Magnetic Trip Current (A)	800A Min - 1600A Max Fixed
Breaking Capacity	Standard Breaking Capacity
Certifications	UL 489, CSA 22.2 No. 5

### FACTORY OPTIONS

Factory Modifications - Left Front Mounting	None
Factory Modifications - Right Front Mounting	None

### TERMINAL LUG DATA

Important Information!	#4AWG - #4/0 AWG, Cu/Al
------------------------	-------------------------

### Dimensions and Weight

Weight (kg / lbs)	2.04 / 4.5
-------------------	------------

---