

Product Details and Certifications

Product: 140U-JD0D3-D20

Description: 200A Molded Case Circuit Breaker, 3-Pole, Frame Size JD, High Breaking Capacity

SYSTEM VOLTAGE DATA

Supply Voltage, Maximum	600V 60Hz
Maximum Available Fault Current	200kA@240V, 100kA@480V, 35kA@600V

CIRCUIT BREAKER

Circuit Breaker Type	Molded Case Circuit Breaker
Application	Inverse Time, Thermal-Magnetic Trip (Fixed Thermal, Adj. Magnetic)
Rated Operational Current (A)	200A
Frame Size	Frame Size JD
Magnetic Trip Current (A)	1000A - 2000A Adjustable
Breaking Capacity	High Breaking Capacity
Certifications	UL 489, CSA 22.2 No. 5

FACTORY OPTIONS

Factory Modifications - Left Front Mounting	None
Factory Modifications - Right Front Mounting	None

TERMINAL LUG DATA

Important Information!	Terminal Lugs are Not Provided
------------------------	--------------------------------

Dimensions and Weight

Weight (kg / lbs)	5.00 / 11.0
-------------------	-------------
