

## Product Details and Certifications

**Product:** 140U-JD6D3-C70

**Description:** 70A Molded Case Circuit Breaker, 3-Pole, Frame Size JD, Medium Breaking Capacity

### SYSTEM VOLTAGE DATA

Supply Voltage, Maximum	600V 60Hz
Maximum Available Fault Current	100kA@240V, 65kA@480V, 25kA@600V

### CIRCUIT BREAKER

Circuit Breaker Type	Molded Case Circuit Breaker
Application	Inverse Time, Thermal-Magnetic Trip (Fixed Thermal, Adj. Magnetic)
Rated Operational Current (A)	70A
Frame Size	Frame Size JD
Magnetic Trip Current (A)	Frame Only, Range Determined By Trip Unit
Breaking Capacity	Medium Breaking Capacity
Certifications	UL 489, CSA 22.2 No. 5

### FACTORY OPTIONS

Factory Modifications - Left Front Mounting	None
Factory Modifications - Right Front Mounting	None

### TERMINAL LUG DATA

Important Information!	Terminal Lugs are Not Provided
------------------------	--------------------------------

### Dimensions and Weight

Weight (kg / lbs)	4.55 / 10.0
-------------------	-------------

---