

Product Details

Product: 140U-K0D3-D10

Description: Molded Case Circuit Breaker, 400A, K-Frame, 100 kA, T/M - Fixed Thermal / Adjustable Magnetic, Rated Current 100A



Representative Photo Only (actual product may vary based on configuration selections)

System Data

Supply Voltage	480V 60Hz
Maximum Available Fault Current (at the Breaker)	0 kA

Circuit Breaker Data

Pole Configuration	3 Poles
Interrupt Rating [kA]	100 kA
Protection	T/M - Fixed Thermal / Adjustable Magnetic
Rated Current (A)	100
Rating / Frame Size	400A, K-Frame

Manufacturing

Assembly	Factory Assembled
----------	-------------------

Terminal Lug Data

Important Information!	Terminal Lugs are not Factory Installed. See below to order.
------------------------	--

Internal Control Modules, Factory Installed

Shunt Trip (SNT) and Undervoltage Release (UVT), Left Side Mounting	None
Voltage	None
Auxiliaries (AX), Alarm (AL), Auxiliary/Alarm Combination (AX/AL), Right Side Mounting	None

Mounting Data

Busbar Mounting (Only for Use with 141A Mounting System)	None
--	------

Certifications and Approvals

UL	489
CSA	22.2, No. 5

Dimensions and Weight

Weight (kg / lbs)	5.33 / 11.7
-------------------	-------------
