

## Product Details

**Product:** 140U-K3D3-D25

Description: Molded Case Circuit Breaker, 400A, K-Frame, 30...39 kA, T/M - Fixed Thermal / Adjustable Magnetic, Rated Current 250A



Representative Photo Only (actual product may vary based on configuration selections)

### System Data

---

Supply Voltage	480V 60Hz
Maximum Available Fault Current (at the Breaker)	0 kA

### Circuit Breaker Data

---

Pole Configuration	3 Poles
Interrupt Rating [kA]	35 kA
Protection	T/M - Fixed Thermal / Adjustable Magnetic
Rated Current (A)	250
Rating / Frame Size	400A, K-Frame

### Manufacturing

---

Assembly	Factory Assembled
----------	-------------------

### Terminal Lug Data

---

Important Information!	Terminal Lugs are not Factory Installed. See below to order.
------------------------	--

### Internal Control Modules, Factory Installed

---

Shunt Trip (SNT) and Undervoltage Release (UVT), Left Side Mounting	None
Voltage	None
Auxiliaries (AX), Alarm (AL), Auxiliary/Alarm Combination (AX/AL), Right Side Mounting	None

### Mounting Data

---

Busbar Mounting (Only for Use with 141A Mounting System)	None
--	------

---

**Certifications and Approvals**

---

UL	489
CSA	22.2, No. 5

**Dimensions and Weight**

---

Weight (kg / lbs)	5.33 / 11.7
-------------------	-------------

---