

Product Details and Certifications

Product: 140U-K6L3-D40

Description: Molded Case Circuit Breaker, K-Frame (up to 400A), 60..69 kA, Electronic LS - Long & Short Time, Rated Current 400 A



Representative Photo Only (actual product may vary based on configuration selections)

System Data

Supply Voltage	480V 60Hz
Maximum Available Fault Current (at the Breaker)	0 kA

Circuit Breaker Data

Current Limitation Required?	No
Pole Configuration	3 Poles
Rated Current (A)	400
Protection	Electronic LS - Long & Short Time
Frame Size	K-Frame (up to 400A)
Interrupt Rating [kA]	65 kA

Manufacturing

Assembly	Factory Assembled
----------	-------------------

Ratings Plug Data

Important Information! Ratings Plug is not Factory Installed, but it is necessary for the operation of the Electronic Trip Unit. See below to order.

Ratings Plug (Required for Electronic Trip No. Ratings Plug is not selected, even though required for proper operation. Units)

Terminal Lug Data

Important Information! Terminal Lugs are not Factory Installed. See below to order.

Internal Control Modules, Factory Installed

Shunt Trip (SNT) and Undervoltage Release (UVT), Left Side Mounting	None
Voltage	None

Auxiliaries (AX), Alarm (AL), None
Auxiliary/Alarm Combination
(AX/AL), Right Side Mounting

Mounting Data

Busbar Mounting (Only for Use with 141A None
Mounting System)

Certifications and Approvals

UL	489
CSA	22.2, No. 5
For UL Certifications Directory:	http://data base.u.l.com/cgi-bin/XYV/template/LISEXT/1 FRAME/index.htm