

## Product Details and Certifications

**Product:** 140U-K6D3-D15

Description: Molded Case Circuit Breaker, 400A, K-Frame, T/M - Fixed Thermal / Adjustable Magnetic, Rated Current 150A



Representative Photo Only (actual product may vary based on configuration selections)

**System Data**

---

Supply Voltage	600V 60Hz
Maximum Available Fault Current (at the Breaker)	5 kA

**Circuit Breaker Data**

---

Is a Current Limiting Circuit Breaker Required?	No, a Current Limiting Circuit Breaker is Not Required
Pole Configuration	3 Poles
Interrupt Rating [kA]	35 kA @ 600V, 65 kA @ 480V
Protection	T/M - Fixed Thermal / Adjustable Magnetic
Rated Current (A)	150
Rating / Frame Size	400A, K-Frame

**Manufacturing**

---

Assembly	Factory Assembled
----------	-------------------

**Terminal Lug Data**

---

Important Information!	Terminal Lugs are not Factory Installed. See below to order.
------------------------	--

**Internal Control Modules, Factory Installed**

---

Shunt Trip (SNT) and Undervoltage Release (UVT), Left Side Mounting	None
Voltage	None
Auxiliaries (AX), Alarm (AL), Auxiliary/Alarm Combination (AX/AL), Right Side Mounting	None

**Mounting Data**

---

Busbar Mounting (Only for Use with 141A Mounting System)	None
--	------

## ***Certifications and Approvals***

---

UL	489
CSA	22.2, No. 5
For UL Certifications Directory:	<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>