

Product Details and Certifications

Product: 140U-K6D3-D35

Description: Molded Case Circuit Breaker, 400A, K-Frame, T/M - Fixed Thermal / Adjustable Magnetic, Rated Current 350A



Representative Photo Only (actual product may vary based on configuration selections)

System Data

| | |
|--|-----------|
| Supply Voltage | 600V 60Hz |
| Maximum Available Fault Current (at the Breaker) | 5 kA |

Circuit Breaker Data

| | |
|---|--|
| Is a Current Limiting Circuit Breaker Required? | No, a Current Limiting Circuit Breaker is Not Required |
| Pole Configuration | 3 Poles |
| Interrupt Rating [kA] | 35 kA @ 600V, 65 kA @ 480V |
| Protection | T/M - Fixed Thermal / Adjustable Magnetic |
| Rated Current (A) | 350 |
| Rating / Frame Size | 400A, K-Frame |

Manufacturing

| | |
|----------|-------------------|
| Assembly | Factory Assembled |
|----------|-------------------|

Terminal Lug Data

| | |
|------------------------|--|
| Important Information! | Terminal Lugs are not Factory Installed. See below to order. |
|------------------------|--|

Internal Control Modules, Factory Installed

| | |
|--|------|
| Shunt Trip (SNT) and Undervoltage Release (UVT), Left Side Mounting | None |
| Voltage | None |
| Auxiliaries (AX), Alarm (AL), Auxiliary/Alarm Combination (AX/AL), Right Side Mounting | None |

Mounting Data

| | |
|--|------|
| Busbar Mounting (Only for Use with 141A Mounting System) | None |
|--|------|

Certifications and Approvals

| | |
|----------------------------------|---|
| UL | 489 |
| CSA | 22.2, No. 5 |
| For UL Certifications Directory: | http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm |